



Steel measuring tape for circumference and \emptyset , maximum total measuring range: 2200mm



Order data

Order number	465680 2200
GTIN	2050001061713
Item class	46R

Description

Version:

Steel measuring tape **CJU** for measuring external circumferences and \emptyset of spherical bodies. The spring steel strip is laser scaled on the front with 2 scales, one for circumference and the other for \emptyset . Graduations 1 mm. **Vernier reading 0.1 mm**. Scale graduation error limits to DIN 866.

Note:

Measuring tapes C with reading 0.05 mm and measuring tapes with black coating available on request. Fixed version CJU on request.

Technical description

Measuring range for circumferences	940 - 2200 mm
Measuring range for \emptyset	300 - 700 mm
Tape width	16 mm
Scale divisions	0.1 mm
Tape thickness	0.2 mm
Calibration	G2
Type of product	Measuring tape

Services

Calibration
Circumference tape measure maximum length
3000 mm

026280 3000