

WITTE**Vacuum plate with grid, Type: R2****Order data**

Order number	385030 R2
GTIN	2050001717481
Item class	38L

Description**Version:**

High-tensile aluminium. Can be extended using connectors as part of a modular system.

Supplied with ZeroClamp holes, 12M10, pitch 200 mm.

Application:

Vacuum clamping of plastic, glass, metals, non-ferrous metals, graphite, and other materials.

Supplied with:

1 hose adapter, 1 connection piece, 7 sealing plugs, 1 plug LW12, 2 clamping claws, vacuum hose (1 m), stop discs.

10 m sealing cord (Ø 4 mm).

Note:

Vacuum clamping plates can be extended using connectors as part of a modular system.

Technical description

Weight	10 kg
Intervals	12.5 mm
Width	300 mm
Length	400 mm
Height	32.5 mm
Type of product	Vacuum clamping plate

