

Mitutoyo
Small internal micrometer, Measuring range: 2-2,5mm

Order data

Order number	429100 2-2,5
GTIN	4946368080468
Item class	44A

Description
Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. The micrometer head (**with 2 carbide measuring faces**) is adjusted by a **carbide-tipped** operating pin.

Application:

For accurate measurement of bore diameter and roundness.

Optional extras:

Setting rings No. 484030.

Technical description

Barrel Ø	17 mm
Measurement depth	12 mm
Measuring range	2 - 2.5 mm
Overall length	105 mm
Scale divisions	0.001 mm
Error limit	0.002 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6

Type of product	2-point internal micrometer
-----------------	-----------------------------

Services

Calibration3-point internal micrometer maximum measuring range 20 mm	022500 20
--	-----------

DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200
---	------------