



Digital caliper ABS with measuring tips, Measuring range: 500mm



Order data

Order number	415621 500
GTIN	4045197829924
Item class	42A

Description

Version:

Digital caliper with **absolute scale**, no zeroing required. Large, sharp-contrast digital display. Electronics switch off automatically after 5 minutes. Switches on when moved. The measuring faces are precision-lapped. **With sturdy metal housing.**

Supplied with:

1 battery No. 081560 size CR2032

Technical description

Scale divisions	0.01 mm
Jaw length	150 mm
Reversible reading	mm / inch
Scale divisions	0.0005 in
Internal jaw \varnothing	20 mm
Calibration	A1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	± 0.06 mm
Standard	ISO 13385

Measuring tips	yes
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 500 mm	021010 500
Calibration Calipers / depth gauges maximum measuring range 500 mm	021000 500

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412230