

**Digital caliper ABS with measuring tips, Measuring range: 750mm****Order data**

Order number	415621 750
GTIN	4045197829931
Item class	42A

**Description****Version:**

Digital caliper with **absolute scale**, no zeroing required. Large, sharp-contrast digital display. Electronics switch off automatically after 5 minutes. Switches on when moved. The measuring faces are precision-lapped. **With sturdy metal housing.**

**Supplied with:**

1 battery No. 081560 size CR2032

**Technical description**

Reversible reading	mm / inch
Scale divisions	0.0005 in
Jaw length	150 mm
Scale divisions	0.01 mm
Internal jaw Ø	20 mm
Calibration	A1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Measurement deviation E MPE	± 0.07 mm
Standard	ISO 13385

Measuring tips	yes
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

## Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000
CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000

## Accessories

Screw for depth gauge holder	412230
Button cell / special battery Battery type CR2032	081560 CR2032