

Mitutoyo
Internal micrometer Holtest for measuring blind holes, Measuring range: 25-30mm


Order data

Order number	429005 25-30
GTIN	4946368517216
Item class	44A

Description

Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. Blind hole version. **Measuring faces of hardened steel with titanium coating for long tool life.**

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Measuring depth with extension	240 mm
Barrel Ø	23 mm
Measuring range	25 - 30 mm
Standard measuring depth	90 mm
Dimension a	0.3 mm
Overall length	140 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50

Accessories

Setting ring DIN 2250 C Nominal size Ø 30 mm	484030 30
Setting ring DIN 2250 C Nominal size Ø 28 mm	484030 28
Setting ring DIN 2250 C Nominal size Ø 25 mm	484030 25
Setting ring DIN 2250 C Nominal size Ø 27 mm	484030 27
Extension for internal micrometer Type 3/150	429010 3/150
Setting ring DIN 2250 C Nominal size Ø 26 mm	484030 26