



## White steel measuring tape in a capsule, Band length: 30m



### Order data

Order number	462900 30
GTIN	4007368073611
Item class	46M

### Description

#### Version:

**Capsule:** Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

**Frame:** Light metal frame with ball bearing mounted fast winding and folding crank.

**Tape:** Patented tape start, **flextop coating**. Tape coating, made of transparent, highly flexible plastic, reliably prevents the tape from breaking at the start.

**White steel measuring tape.** Hardened tape, phosphated coating provides corrosion resistance, with wear-resistant synthetic resin coating. Good legibility. With mm graduations throughout.

#### Note:

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

### Technical description

Capsule height	32 mm
Tape width	13 mm
Capsule width	145 mm
Capsule length	175 mm

Type of tape start	A
Band length	30 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

## Services

CalibrationTape measure maximum length 50 m	026240 50
---	-----------