

**Mitutoyo**
**Small internal micrometer, Measuring range: 2,5-3mm**

**Order data**

Order number	429100 2,5-3
GTIN	4946368080475
Item class	44A

**Description**
**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. The micrometer head (**with 2 carbide measuring faces**) is adjusted by **a carbide-tipped** operating pin.

**Application:**

For accurate measurement of bore diameter and roundness.

**Optional extras:**

Setting rings No. 484030.

**Technical description**

Measuring range	2.5 - 3 mm
Barrel Ø	17 mm
Measurement depth	12 mm
Overall length	105 mm
Scale divisions	0.001 mm
Error limit	0.002 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6

Type of product	2-point internal micrometer
-----------------	-----------------------------

## Services

Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20
---	-----------

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
--	------------

## Accessories

Setting ring DIN 2250 C Nominal size $\varnothing$ 3 mm	484030 3
---	----------