

**Glass fibre measuring tape in a capsule, Band length: 30m****Order data**

Order number	463300 30
GTIN	4007368073017
Item class	46M

**Description****Version:**

**Capsule:** Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

**Frame:** Light metal frame with ball bearing mounted fast winding and folding crank.

**Glass fibre measuring tape. Extremely** buckling-resistant **and flexible**, weather-proof, and resistant to many chemicals. **Electrically non-conducting.** Good legibility. With cm graduations.

**Note:**

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

**Technical description**

Tape width	13 mm
Capsule width	175 mm
Capsule length	210 mm
Capsule height	32 mm
Type of tape start	A

Band length	30 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

**Services**

CalibrationTape measure maximum length 50 m	026240 50
---	-----------