

Mitutoyo**Internal micrometer set Holtest, Measuring range: 6-12mm****Order data**

Order number	429050 6-12
GTIN	4946368517575
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Supplied with:

Internal micrometers No. 429000. Setting rings similar to No. 484030, extension 100 mm No. 429010.

Technical description

Setting ring Ø	8 / 10 mm
Number of micrometers	3
Measuring range	6 - 12 mm
Error limit	0.004 mm
Scale divisions	0.001 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

020550 6-12

Calibration Internal micrometer set Measuring range 6-12 mm

Accessories

Extension for internal micrometer Type 1/100	429010 1/100
Internal micrometer Holtest Measuring range 8-10 mm	429000 8-10
Internal micrometer Holtest Measuring range 6-8 mm	429000 6-8
Setting ring DIN 2250 C Nominal size Ø 11 mm	484030 11
Setting ring DIN 2250 C Nominal size Ø 7 mm	484030 7
Internal micrometer Holtest Measuring range 10-12 mm	429000 10-12
Setting ring DIN 2250 C Nominal size Ø 9 mm	484030 9