

Mitutoyo**Internal micrometer set Holtest, Measuring range: 12-20mm****Order data**

Order number	429050 12-20
GTIN	4946368518039
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Supplied with:

Internal micrometers No. 429000. Setting rings similar to No. 484030, extension 150 mm No. 429010.

Technical description

Setting ring \varnothing	16 mm
Number of micrometers	2
Measuring range	12 - 20 mm
Error limit	0.004 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	S6
Type of product	3-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 12-20 mm	020550 12-20
---	--------------

Accessories

Internal micrometer Holtest Measuring range 12-16 mm	429000 12-16
Internal micrometer Holtest Measuring range 16-20 mm	429000 16-20
Extension for internal micrometer Type 2/150	429010 2/150
Setting ringDIN 2250 C Nominal size Ø 18 mm	484030 18
Setting ringDIN 2250 C Nominal size Ø 15 mm	484030 15