

Mitutoyo**Small internal micrometer, Measuring range: 4-5mm****Order data**

Order number	429100 4-5
GTIN	4946368080499
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. The micrometer head (**with 2 carbide measuring faces**) is adjusted by a **carbide-tipped** operating pin.

Application:

For accurate measurement of bore diameter and roundness.

Optional extras:

Setting rings No. 484030.

Technical description

Measurement depth	22 mm
Measuring range	4 - 5 mm
Overall length	115 mm
Barrel Ø	17 mm
Scale divisions	0.001 mm
Error limit	0.002 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6

Type of product	2-point internal micrometer
-----------------	-----------------------------

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
--	------------

Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20
---	-----------

Accessories

Setting ring DIN 2250 C Nominal size Ø 4 mm	484030 4
---	----------

Setting ring DIN 2250 C Nominal size Ø 5 mm	484030 5
---	----------