

**Mitutoyo****Internal micrometer set Holtest, Measuring range: 20-50mm****Order data**

Order number	429050 20-50
GTIN	4946368518046
Item class	44A

**Description****Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

**Supplied with:**

Internal micrometers No. 429000. Setting rings similar to No. 484030, extension 150 mm No. 429010.

**Technical description**

Number of micrometers	4
Measuring range	20 - 50 mm
Setting ring $\varnothing$	25 / 40 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

### Services

CalibrationInternal micrometer set Measuring range 20-50 mm	020550 20-50
---	--------------

### Accessories

Setting ringDIN 2250 C Nominal size Ø 45 mm	484030 45
Internal micrometer Holtest Measuring range 40-50 mm	429000 40-50
Internal micrometer Holtest Measuring range 30-40 mm	429000 30-40
Internal micrometer Holtest Measuring range 25-30 mm	429000 25-30
Extension for internal micrometer Type 3/150	429010 3/150
Internal micrometer Holtest Measuring range 20-25 mm	429000 20-25
Setting ringDIN 2250 C Nominal size Ø 35 mm	484030 35
Setting ringDIN 2250 C Nominal size Ø 27 mm	484030 27
Setting ringDIN 2250 C Nominal size Ø 22 mm	484030 22