

Mitutoyo
Internal micrometer Holtest for measuring blind holes, Measuring range: 50-63mm


Order data

Order number	429005 50-63
GTIN	4946368517247
Item class	44A

Description

Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. Blind hole version. **Measuring faces of hardened steel with titanium coating for long tool life.**

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Overall length	156 mm
Barrel Ø	23 mm
Standard measuring depth	105 mm
Dimension a	0.3 mm
Measuring depth with extension	255 mm
Measuring range	50 - 63 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 100 mm	022500 100

Accessories

Setting ring DIN 2250 C Nominal size Ø 55 mm	484030 55
Setting ring DIN 2250 C Nominal size Ø 60 mm	484030 60
Setting ring DIN 2250 C Nominal size Ø 50 mm	484030 50
Extension for internal micrometer Type 4/150	429010 4/150