

**Polyamide coated steel measuring tape in a capsule, Band length: 20m****Order data**

Order number	463100 20
GTIN	4007368074847
Item class	46M

**Description****Version:**

**Capsule:** Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

**Frame:** Light metal frame with ball bearing mounted fast winding and folding crank.

**Tape:** Patented tape start, **flextop coating**. Tape coating, made of transparent, highly flexible plastic, reliably prevents the tape from breaking at the start.

**Polyamide coated steel measuring tape.** Break-proof, with good flexibility. Non-buckling spring steel. **High abrasion resistance**, weather-proof and resistant to many chemicals and oils. With mm graduations throughout.

**Note:**

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

**Technical description**

Capsule length	175 mm
Capsule width	145 mm
Tape width	13 mm
Capsule height	32 mm

Type of tape start	A
Band length	20 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

## Services

CalibrationTape measure maximum length 50 m	026240 50
---	-----------