

**Polyamide coated steel measuring tape in a capsule, Band length: 30m****Order data**

Order number	463100 30
GTIN	4007368074861
Item class	46M

Description**Version:**

Capsule: Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

Frame: Light metal frame with ball bearing mounted fast winding and folding crank.

Tape: Patented tape start, **flextop coating**. Tape coating, made of transparent, highly flexible plastic, reliably prevents the tape from breaking at the start.

Polyamide coated steel measuring tape. Break-proof, with good flexibility. Non-buckling spring steel. **High abrasion resistance**, weather-proof and resistant to many chemicals and oils. With mm graduations throughout.

Note:

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

Technical description

Tape width	13 mm
Capsule height	32 mm
Capsule width	175 mm
Capsule length	210 mm

Type of tape start	A
Band length	30 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 50 m	026240 50
---	-----------