

Mitutoyo
Digital internal micrometer set, Measuring range: 6-12mm

Order data

Order number	429112 6-12
GTIN	4946368562919
Item class	44A

Description
Version:

Direct reading from clear digital display. Reliable and accurate measuring – without vernier.

“Function Lock” prevents accidental displacement of the zero point.

Low power consumption. With battery charge status and error display.

Measuring faces and wearing parts of carbide, from size 12 -25 measuring faces of hardened steel with titanium coating for long tool life.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Digital internal micrometers No. 429110, setting rings.

Technical description

Setting ring \varnothing	8 / 10 mm
Measuring range	6 - 12 mm
Number of micrometers	3

Number of setting rings	2
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

Calibration Internal micrometer set Measuring range 6-12 mm	020550 6-12
---	-------------

Accessories

Connecting cable with data switch Type USB2	497445 USB2
Extension for internal micrometer Type 1/100	429010 1/100
Receiver / USB keyboard interface Type	498965
Setting ring DIN 2250 C Nominal size Ø 11 mm	484030 11
Connecting cable with data switch Type D2	497445 D2
Connecting cable with data switch Type D1	497445 D1
Setting ring DIN 2250 C Nominal size Ø 9 mm	484030 9
Multi-receiver / USB keyboard interface Type	498975
Button cell / special battery Battery type 357	081560 357
Setting ring DIN 2250 C Nominal size Ø 7 mm	484030 7
Transmitter Type S16E	498966 S16E