

**Mitutoyo****Digital internal micrometer, Measuring range: 30-40mm****Order data**

Order number	429110 30-40
GTIN	4946368563459
Item class	44A

**Description****Version:**

**Direct reading from clear digital display. Reliable and accurate measuring – without vernier.**

“Function Lock” prevents accidental displacement of the zero point.

Low power consumption. With battery charge status and error display.

**Measuring faces and wearing parts of carbide, from size 12 -16 measuring faces of hardened steel with titanium coating for long tool life.**

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Data cable No. 497445, extensions No. 429010, setting rings No. 484030.

**Note:**

Available up to a measuring range 300 mm on request.

**Technical description**

Dimension a	0.3 mm
Measuring depth with extension	252 mm
Measuring range	30 - 40 mm
Standard measuring depth	102 mm
Error limit	0.003 mm

Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

## Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50

## Accessories

Setting ring DIN 2250 C Nominal size Ø 36 mm	484030 36
Setting ring DIN 2250 C Nominal size Ø 40 mm	484030 40
Connecting cable with data switch Type D1	497445 D1
Connecting cable with data switch Type USB2	497445 USB2
Setting ring DIN 2250 C Nominal size Ø 30 mm	484030 30
Transmitter Type S16E	498966 S16E
Connecting cable with data switch Type D2	497445 D2
Multi-receiver / USB keyboard interface Type	498975
Receiver / USB keyboard interface Type	498965

Setting ringDIN 2250 C Nominal size Ø 35 mm	484030 35
Setting ringDIN 2250 C Nominal size Ø 34 mm	484030 34
Extension for internal micrometer Type 3/150	429010 3/150
Setting ringDIN 2250 C Nominal size Ø 38 mm	484030 38
Setting ringDIN 2250 C Nominal size Ø 32 mm	484030 32
Button cell / special battery Battery type 357	081560 357