

**Mitutoyo****Internal micrometer set Holtest, Measuring range: 50-100mm****Order data**

Order number	429050 50-100
GTIN	4946368518053
Item class	44A

**Description****Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

**Supplied with:**

Internal micrometers No. 429000. Setting rings similar to No. 484030, extension 150 mm No. 429010.

**Technical description**

Setting ring $\varnothing$	62 / 87 mm
Number of micrometers	4
Measuring range	50 - 100 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

### Services

CalibrationInternal micrometer set Measuring range 50-100 mm	020550 50-100
--	---------------

### Accessories

Extension for internal micrometer Type 4/150	429010 4/150
Setting ringDIN 2250 C Nominal size Ø 80 mm	484030 80
Setting ringDIN 2250 C Nominal size Ø 90 mm	484030 90
Internal micrometer Holtest Measuring range 75-88 mm	429000 75-88
Internal micrometer Holtest Measuring range 50-63 mm	429000 50-63
Setting ringDIN 2250 C Nominal size Ø 55 mm	484030 55
Setting ringDIN 2250 C Nominal size Ø 70 mm	484030 70
Internal micrometer Holtest Measuring range 87-100 mm	429000 87-100
Internal micrometer Holtest Measuring range 62-75 mm	429000 62-75