

**Mitutoyo****Digital three-point internal micrometer set, Measuring range: 25-50mm****Order data**

Order number	429260 25-50
GTIN	4946368636733
Item class	44A

**Description****Version:**

Borematic quick blind hole micrometer for **3-point internal measurement**. Large LCD display with 11 mm character height for clear and error-free reading. **Display can be rotated 330°**. The measuring probes centre the micrometer automatically in the bore and ensure easy handling. The measuring probes are adjusted without any error by a **carbide cone**.

**Advantage:**

Very quick measurement with high repetition accuracy due to pistol grip and constant measuring force.

**Function:**

- **Data storage button saves the measurement result (for instance in inaccessible measurement positions).**
- **Zero point / absolute size enables zeroing at any position.**
- **Good / Reject display for easy checking against tolerance values.**
- **Quick adjustment for quick spanning of the distance to be measured.**

**Supplied with:**

Digital internal micrometers No. 429250, setting rings.

**Technical description**

Number of setting rings	2
Setting ring Ø	30 / 40 mm
Number of measuring heads	3
Measuring range	25 - 50 mm
Error limit	0.006 mm
Scale divisions	0.001 mm
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Calibration	S6
Type of product	3-point bore gauge

## Services

CalibrationInternal micrometer set Measuring range 25-50 mm	020550 25-50
---	--------------

## Accessories

Setting ringDIN 2250 C Nominal size Ø 27 mm	484030 27
Button cell / special battery Battery type 357	081560 357
Setting ringDIN 2250 C Nominal size Ø 35 mm	484030 35
Transmitter Type S1	498966 S1
Connecting cable Type D1	497080 D1
Connecting cable Type D2	497080 D2
Setting ringDIN 2250 C Nominal size Ø 45 mm	484030 45
Connecting cable Type USB2	497080 USB2

Receiver / USB keyboard interface Type	498965
Extension for internal micrometer Type 3/150	429010 3/150
Multi-receiver / USB keyboard interface Type	498975