

**Mitutoyo**
**Internal micrometer Holtest for measuring blind holes, Measuring range: 75-88mm**


## Order data

Order number	429005 75-88
GTIN	4946368517261
Item class	44A

## Description

### Version:

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. Blind hole version. **Measuring faces of hardened steel with titanium coating for long tool life.**

### Optional extras:

Extensions No. 429010. Setting rings No. 484030.

## Technical description

Measuring depth with extension	255 mm
Dimension a	0.3 mm
Standard measuring depth	105 mm
Overall length	156 mm
Barrel Ø	23 mm
Measuring range	75 - 88 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

## Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 100 mm	022500 100

## Accessories

Setting ring DIN 2250 C Nominal size $\varnothing$ 80 mm	484030 80
Setting ring DIN 2250 C Nominal size $\varnothing$ 75 mm	484030 75
Extension for internal micrometer Type 4/150	429010 4/150
Setting ring DIN 2250 C Nominal size $\varnothing$ 85 mm	484030 85