

**Mitutoyo****Internal micrometer set Holtest, Measuring range: 100-200mm****Order data**

Order number	429050 100-200
GTIN	4946368518060
Item class	44A

**Description****Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

**Supplied with:**

Internal micrometers No. 429000. Setting rings similar to No. 484030, extension 150 mm No. 429010.

**Technical description**

Setting ring Ø	125 / 175 mm
Measuring range	100 - 200 mm
Number of micrometers	4
Error limit	0.01 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

**Services**

020550 100-200

Calibration Internal micrometer set Measuring range  
100-200 mm

## Accessories

Internal micrometer Holtest Measuring range 100-125 mm	429000 100-125
Setting ring DIN 2250 C Nominal size Ø 180 mm	484030 180
Setting ring DIN 2250 C Nominal size Ø 140 mm	484030 140
Internal micrometer Holtest Measuring range 125-150 mm	429000 125-150
Internal micrometer Holtest Measuring range 150-175 mm	429000 150-175
Setting ring DIN 2250 C Nominal size Ø 110 mm	484030 110
Extension for internal micrometer Type 4/150	429010 4/150
Setting ring DIN 2250 C Nominal size Ø 160 mm	484030 160
Internal micrometer Holtest Measuring range 175-200 mm	429000 175-200