

Mitutoyo
Digital internal micrometer, Measuring range: 50-63mm

Order data

Order number	429110 50-63
GTIN	4946368563022
Item class	44A

Description
Version:

Direct reading from clear digital display. Reliable and accurate measuring – without vernier.

“Function Lock” prevents accidental displacement of the zero point.

Low power consumption. With battery charge status and error display.

Measuring faces and wearing parts of carbide, from size 12 -16 measuring faces of hardened steel with titanium coating for long tool life.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497445, extensions No. 429010, setting rings No. 484030.

Note:

Available up to a measuring range 300 mm on request.

Technical description

Measuring range	50 - 63 mm
Dimension a	0.3 mm
Measuring depth with extension	252 mm
Standard measuring depth	102 mm
Error limit	0.003 mm

Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration3-point internal micrometer maximum measuring range 100 mm	022500 100
DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Transmitter Type S16E	498966 S16E
Connecting cablewith data switch Type D2	497445 D2
Setting ringDIN 2250 C Nominal size Ø 45 mm	484030 45
Connecting cablewith data switch Type D1	497445 D1
Button cell / special battery Battery type 357	081560 357
Setting ringDIN 2250 C Nominal size Ø 60 mm	484030 60
Connecting cablewith data switch Type USB2	497445 USB2
Extension for internal micrometer Type 4/150	429010 4/150
Setting ringDIN 2250 C Nominal size Ø 50 mm	484030 50

Receiver / USB keyboard interface Type	498965
Multi-receiver / USB keyboard interface Type	498975