

Mitutoyo
Digital internal micrometer set, Measuring range: 25-50mm

Order data

Order number	429112 25-50
GTIN	4946368562933
Item class	44A

Description
Version:

Direct reading from clear digital display. Reliable and accurate measuring – without vernier.

“Function Lock” prevents accidental displacement of the zero point.

Low power consumption. With battery charge status and error display.

Measuring faces and wearing parts of carbide, from size 12 -25 measuring faces of hardened steel with titanium coating for long tool life.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Digital internal micrometers No. 429110, setting rings.

Technical description

Measuring range	25 - 50 mm
Number of setting rings	2
Setting ring \varnothing	30 / 40 mm

Number of micrometers	3
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 25-50 mm	020550 25-50
---	--------------

Accessories

Setting ringDIN 2250 C Nominal size Ø 28 mm	484030 28
Button cell / special battery Battery type 357	081560 357
Setting ringDIN 2250 C Nominal size Ø 35 mm	484030 35
Multi-receiver / USB keyboard interface Type	498975
Connecting cablewith data switch Type D2	497445 D2
Setting ringDIN 2250 C Nominal size Ø 45 mm	484030 45
Extension for internal micrometer Type 3/150	429010 3/150
Connecting cablewith data switch Type USB2	497445 USB2
Receiver / USB keyboard interface Type	498965
Transmitter Type S16E	498966 S16E
Connecting cablewith data switch Type D1	497445 D1