

## TAJIMA

**Tape measure, non-slip casing extra sturdy, Band length: 5/25 m**



### Order data

Order number	462330 5/25
GTIN	4975364029133
Item class	46R

### Description

#### Version:

- **Tape with particularly high buckling stability.**
- **Totally shock-proof plastic housing with removable belt clip.**
- **Automatic tape return and stop.**
- **Shock absorber reduces load during tape return.**
- **Sliding end hook.**
- **Tape measure printed black/red on yellow, acrylic coated for high abrasion resistance**
- **Long-lasting spring of high grade steel.**
- **Additionally with rubberised casing.**
- **Tape printed both sides.**

Calibration: G1

Standard: EG II

Tape width: 25 mm

Body length: 67 mm

Body width: 28 mm

Body height: 63 mm

### Technical description

Body height	63 mm
Tape width	25 mm
Body length	67 mm

Body width	28 mm
Band length	5 m
Standard	EG II
Calibration	G1
Type of product	Locking tape measure in a frame capsule housing

### Services

Calibration Locking tape measure maximum length 5/2 m	016140 5/2
Labelling laser-etched Type	018940
30/2	026250 30/2
Calibration Tape measure maximum length 5/2 m	026240 5/2