

**Tajima****Tape measure, non-slip casing extra sturdy, Band length: 5/25m****Order data**

Order number	462330 5/25
GTIN	4975364029133
Item class	46R

**Description****Version:**

- **Tape measure with particularly high buckling stability.**
- **Totally shock-proof plastic housing with removable belt clip.**
- **Automatic tape return and stop.**
- **Shock absorber reduces the impact at tape return.**
- **Sliding end hook.**
- **Tape measure printed black/red on yellow, acrylic coated for high abrasion resistance.**
- **Long-lasting spring made of high grade steel.**
- **Additionally with rubberised casing.**
- **Tape printed both sides.**

**Technical description**

Body height	63 mm
Tape width	25 mm
Body length	67 mm
Body width	28 mm
Band length	5 m
Standard	EG II
Calibration	G1

Type of product

Measuring tape

---

**Services**

CalibrationTape measure maximum length 5/2 m

026240 5/2