



Laser distance meter DISTO™, Type: D510

Order data

Order number	465550 D510
GTIN	7640110694237
Item class	47C

Description

Version:

Impact resistant plastic casing with easy-to-use keypad with symbols. High quality **Leica glass lens** in a particularly temperature-resistant and sturdy **magnesium casing**. Illuminated and rotating colour display for optimum legibility. Power Range Technologie™ for measurements **up to 80 m without target board**. Laser class 2 to IEC 825-1. Data transfer via Bluetooth® Smart; also by smartphone using the free app Leica "DISTO™ sketch" (Android from version 4.3, Apple from iPhone 4s).

Versatile tool for indoor and outdoor use. Ergonomic design with softgrip rubberised surface, rests easily in the hand. Multi-function endpiece for measuring from corners. With **digital target searcher** (4× zoom) for measurements at long distances or in sunshine. The **integral 360° inclination sensor** shows the inclination of an object when the casing is placed directly on it, thus permitting indirect height measurement.

Supplied with:

Protective holder and wrist strap. Includes 2 batteries.

Optional extras:

Measurement scale No. 468558.

Note:

Data transfer via Bluetooth® Smart; also by smartphone using a Leica "DISTO™ Plan" app (Android from version 4.3, Apple from iPhone 4s). Easy generation of sketches.

Reversible reading: mm / inch

IP Index of Protection: IP 65

Measuring accuracy: ±1.0 mm

Threaded socket for stand: 1/4 inch

multi-function endpiece: true

Range: 200 m

Addition/subtraction: true

Minimum / maximum measurements: true

Technical description

Laser class to IEC 825–1	2
Material of the housing	
Reversible reading	mm / inch
Type of product	Workshop straight edge with graduations on both sides