

**Mitutoyo**
**Digital internal micrometer, Measuring range: 10-12mm**

**Order data**

Order number	429110 10-12
GTIN	4946368562971
Item class	44A

**Description**
**Version:**

**Direct reading from clear digital display. Reliable and accurate measuring – without vernier.**

“Function Lock” prevents accidental displacement of the zero point.

Low power consumption. With battery charge status and error display.

**Measuring faces and wearing parts of carbide, from size 12 -16 measuring faces of hardened steel with titanium coating for long tool life.**

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Data cable No. 497445, extensions No. 429010, setting rings No. 484030.

**Note:**

Available up to a measuring range 300 mm on request.

**Technical description**

Standard measuring depth	45 mm
Dimension a	2 mm
Measuring range	10 - 12 mm
Measuring depth with extension	145 mm
Error limit	0.002 mm

Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

## Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20

## Accessories

Extension for internal micrometer Type 1/100	429010 1/100
Connecting cable with data switch Type D2	497445 D2
Connecting cable with data switch Type USB2	497445 USB2
Transmitter Type S16E	498966 S16E
Setting ring DIN 2250 C Nominal size Ø 11 mm	484030 11
Multi-receiver / USB keyboard interface Type	498975
Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type D1	497445 D1
Button cell / special battery Battery type 357	081560 357

Setting ringDIN 2250 C Nominal size Ø 10 mm	484030 10
Setting ringDIN 2250 C Nominal size Ø 12 mm	484030 12