

Garant
Granite plate Accuracy class 0, Length×Width: 400X400mm

Order data

| | |
|--------------|----------------|
| Order number | 430190 400X400 |
| GTIN | 4045197435750 |
| Item class | 41C |

Description
Version:

Specially selected natural granite.

- **Free from defects, homogeneous structure.**
- **Resistant to deflection and to warping.**
- **Absolutely rust-proof and acid resistant, low thermal conductivity.**
- **Micro-fine machine surface (diamond lapped). Within all the permissible tolerances.**
- **Ground outside edges, visually true.**
- **For static determination of position, contact points (steel ball inserts) are fitted to the underside.**
- **Harder than hardened steel (Mohs hardness scale 6 – 7), non-magnetic and electrically non-conductive.**

Accuracy:

Final manufacturing and inspection take place in computer-controlled climatic rooms. The used measuring equipment guarantees the exact connection to national and international calibration laboratories.

DIN 876/0 – Precision diamond lapped for inspection.

Supplied with:

Supplied with test certificate, transport packing. Including rubber feet.

Note:

On request: Stainless steel screw inserts, steel T-slot rails (steel T-slot rails not available for No. 430190), accuracy 000, other sizes, intermediate sizes. Delivery excluded.

Technical description

| | |
|-----------|----------|
| Flatness | 0.006 mm |
| Thickness | 50 mm |

| | |
|-----------------------|---------------------------------|
| Weight | 25 kg |
| Number of rubber feet | 4 |
| Standard | DIN 876 |
| Accuracy | 0 mm |
| Test certificate | Manufacturer's test certificate |
| Type of product | Graduated plate |

Accessories

| | |
|--|------------|
| Care product for granite Contents 0,5 l | 431840 0,5 |
| Cleaner for natural granite Contents 0,5 l | 431841 0,5 |