

**Mitutoyo****Digital internal micrometer set, Measuring range: 50-75mm****Order data**

Order number	429112 50-75
GTIN	2050001062277
Item class	44A

**Description****Version:**

**Direct reading from clear digital display. Reliable and accurate measuring – without vernier.**

“Function Lock” prevents accidental displacement of the zero point.

Low power consumption. With battery charge status and error display.

**Measuring faces and wearing parts of carbide, from size 12 -25 measuring faces of hardened steel with titanium coating for long tool life.**

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

Digital internal micrometers No. 429110, setting rings.

**Technical description**

Measuring range	50 - 75 mm
Setting ring Ø	62 mm
Number of micrometers	2

Number of setting rings	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

## Services

Calibration Internal micrometer set Measuring range 50-75 mm	020550 50-75
--	--------------

## Accessories

Connecting cable with data switch Type USB2	497445 USB2
Receiver / USB keyboard interface Type	498965
Transmitter Type S16E	498966 S16E
Button cell / special battery Battery type 357	081560 357
Multi-receiver / USB keyboard interface Type	498975
Extension for internal micrometer Type 4/150	429010 4/150
Connecting cable with data switch Type D1	497445 D1
Connecting cable with data switch Type D2	497445 D2
Setting ring DIN 2250 C Nominal size Ø 55 mm	484030 55
Setting ring DIN 2250 C Nominal size Ø 70 mm	484030 70