



Laser distance meter, Range: 60m



Order data

Order number	465540 60
GTIN	4045197838728
Item class	42I

Description

Version:

Attractively-priced laser distance measurement device for quick and easy performance of standard measurement tasks. Ergonomically shaped 2-component casing. Soft-touch keyboard with self-explanatory symbols. Background lighting of LCD display can be activated. Graphical symbols in the display support the user during measurement operations. Laser class 2.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Accuracy:

Deviation ± 1.5 mm over a 10 m measuring length under optimum conditions.

Supplied with:

Includes 2x batteries No. 081551 LR3, belt pocket and wrist strap.

Technical description

Measuring accuracy	± 1.5 mm
indirect measurements (Pythagoras)	yes

Height	28 mm
dynamic measurement	yes
Addition/subtraction	yes
Minimum / maximum measurements	yes
Weight	100 g
acoustic confirmation of measurements	yes
Range	60 m
Battery life (measurements)	4000
IP Index of Protection	IP 54
Measured value memory	20
Length	110 mm
Automatic switch-off	3 min
Power supply	2× 081551 LR3
Surface and volume calculations	yes
Width	46 mm
Article no of the battery / rechargeable battery fitted	081551 LR3
Number of batteries contained	2
Power supply	Battery-powered
Type of product	Distance meter

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------