



## Laser distance meter, Range: 110m



### Order data

Order number	465540 110
GTIN	4045197838735
Item class	42I

### Description

#### Version:

Attractively-priced laser distance measurement device for quick and easy performance of standard measurement tasks. Ergonomically shaped 2-component casing. Soft-touch keyboard with self-explanatory symbols. Background lighting of LCD display can be activated. Graphical symbols in the display support the user during measurement operations. Laser class 2.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Accuracy:

Deviation  $\pm 1.5$  mm over a 10 m measuring length under optimum conditions.

#### Supplied with:

Includes 2x batteries No. 081551 LR3, belt pocket and wrist strap.

### Technical description

Addition/subtraction	yes
Measuring accuracy	$\pm 1.5$ mm

acoustic confirmation of measurements	yes
IP Index of Protection	IP 54
dynamic measurement	yes
Minimum / maximum measurements	yes
Weight	100 g
Automatic switch-off	3 min
Battery life (measurements)	4000
indirect measurements (Pythagoras)	yes
Measured value memory	20
Surface and volume calculations	yes
Range	110 m
Height	28 mm
Length	110 mm
Width	46 mm
Power supply	2× 081551 LR3
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081551 LR3
Power supply	Battery-powered
Type of product	Distance meter

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------