



Knurl forming tool universal, Shank size: 25mm



Order data

Order number	290084 25
GTIN	4030741324468
Item class	29H

Description

Version:

Modular design: Can be used universally as right-hand or left-hand version.

Grub screws in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

Top face of the shank = tip height

Technical description

Shank height	20 mm
Working range	8 - 200 mm
for knurl bore $\varnothing d_2$	6 mm
for knurl width w	8 mm
Shank width	25 mm
for knurl $\varnothing d_1$	20 mm
for knurled countersunk $\varnothing d_3$	13 mm

Closure stud	299925 2
Disc	299927 2
Cutting direction for knurl profile	Left-hand and right-hand
Type of product	RAA 1×AA
	Self-centering knurling tool

Accessories

Closure stud Type 2	299925 2
Disc Type 2	299927 2