



Knurl forming tool universal, Shank size: 20mm



Order data

Order number	290090 20
GTIN	4030741325175
Item class	29H

Description

Version:

Modular design: Can be used universally as right-hand or left-hand version.

Grub screws in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

Technical description

for knurl width w	8 mm
Shank height	20 mm
Working range	10 - 110 mm
Shank width	20 mm
for knurl bore $\varnothing d_2$	6 mm
for knurl $\varnothing d_1$	20 mm
for knurled countersunk $\varnothing d_3$	13 mm
Closure stud	299925 2

Disc	299927 2
Cutting direction	Left-hand and right-hand
for knurl profile	RAA 2×AA
Type of product	Self-centering knurling tool

Accessories

Closure stud Type 2	299925 2
Disc Type 2	299927 2