

**Mitutoyo**
**Digital internal micrometer, Measuring range: 125-150mm**

**Order data**

Order number	429110 125-150
GTIN	2050001062239
Item class	44A

**Description**
**Version:**

**Direct reading from clear digital display. Reliable and accurate measuring – without vernier.**

“Function Lock” prevents accidental displacement of the zero point.

Low power consumption. With battery charge status and error display.

**Measuring faces and wearing parts of carbide, from size 12 -16 measuring faces of hardened steel with titanium coating for long tool life.**

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Data cable No. 497445, extensions No. 429010, setting rings No. 484030.

**Note:**

Available up to a measuring range 300 mm on request.

**Technical description**

Measuring range	125 - 150 mm
Dimension a	12.4 mm
Measuring depth with extension	301 mm
Standard measuring depth	151 mm
Error limit	0.005 mm

Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

## Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 200 mm	022500 200

## Accessories

Setting ring DIN 2250 C Nominal size Ø 140 mm	484030 140
Transmitter Type S16E	498966 S16E
Multi-receiver / USB keyboard interface Type	498975
Connecting cable with data switch Type D2	497445 D2
Button cell / special battery Battery type 357	081560 357
Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type D1	497445 D1
Extension for internal micrometer Type 4/150	429010 4/150
Setting ring DIN 2250 C Nominal size Ø 125 mm	484030 125

Connecting cable with data switch Type USB2

497445 USB2