



Modular vice, Jaw width A: 125mm



Order data

Order number	362100 125
GTIN	2050001077479
Item class	35G

Description

Version:

- Simple mechanical actuation (up to 3.5 t).
- Easy adjustment of jaw opening.
- Machine vice with pull-down jaws.
- Case-hardened HRC 60.
- Parallelism 0.02 mm.

Supplied with:

Supplied with pull-down jaws, 1 workpiece backstop, 2 T-nuts No. 362160 size 16/16, 1 clamping wrench, 1 cross-bar wrench.

Note:

For other T-nuts see No. 362160.

Technical description

Weight	17 kg
Base body height G	40 mm
Clamping range b	150 mm
Colour code for suitable accessories	Gerardi 125
Transverse tenon slot n	16 mm
Jaw width A	125 mm

Jaw height C	40 mm
Longitudinal tenon slot l	16 mm
Overall length L	345 mm
maximum clamping force at 60 Nm	25 kN
Series	Gerardi 125
Type of product	Machine vice

Accessories

Prismatic jaw (piece) for jaw width 125 mm	362125 125
Pair of T-nuts T-slot dimension B / keyway 12/16 mm	362160 12/16
Modular element fixed (piece) for jaw width 125 mm	362150 125
Pair of T-nuts T-slot dimension B / keyway 20/16 mm	362160 20/16
Pair of T-nuts T-slot dimension B / keyway 16/16 mm	362160 16/16
Pair of T-nuts T-slot dimension B / keyway 14/16 mm	362160 14/16
Smooth front jaw, hard (piece) for jaw width 125 mm	362147 125
Longitudinally serrated front jaw (piece) for jaw width 125 mm	362146 125
Pair of T-nuts T-slot dimension B / keyway 18/16 mm	362160 18/16
Smooth front jaw, soft (piece) for jaw width 125 mm	362148 125
Complete clamping element (piece) for jaw width 125 mm	362144 125
Movable jaw (piece) for jaw width 125 mm	362143 125
Pair of clamps for jaw width 125 mm	362120 125
Modular element movable (piece) for jaw width 125 mm	362145 125