



## Whistle Notch side lock arbor Form ADB, BT 50 short, Whistle Notch side lock arbor: 8 mm



### Order data

Order number	302726 8
GTIN	2050001921574
Item class	36E

### Description

#### Version:

With clamping screw and stop screw.

#### Optional extras:

Pull studs (PS) No. 308760 – 308806.

Overhang dimension A: 63 mm

External  $\varnothing$  D: 28 mm

Spare clamping screw 309900: 8

### Technical description

Clamping $\varnothing$ D <sub>1</sub>	8 mm
External $\varnothing$ D	28 mm
Overhang dimension A	63 mm
Spare clamping screw 309900	8
Adapter	BT 50 short
Norm	DIN 6359
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	ADB

Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC

---

## Accessories

Pull stud 45° sealed suitable for steep tapers 50	308765 50
Pull-stud 60° sealed suitable for steep tapers 50	308780 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Pull stud 45° sealed suitable for steep tapers 50	308760 50