



Whistle Notch side lock arbor Form ADB, BT 50 short, Whistle Notch side lock arbor: 32 mm



Order data

Order number	302726 32
GTIN	2050001921949
Item class	36E

Description

Version:

With clamping screw and stop screw.

Optional extras:

Pull studs (PS) No. 308760 – 308806.

Overhang dimension A: 105 mm

External \varnothing D: 72 mm

Spare clamping screw 309900: 32

Technical description

Clamping \varnothing D ₁	32 mm
Overhang dimension A	105 mm
External \varnothing D	72 mm
Spare clamping screw 309900	32
Adapter	BT 50 short
Norm	DIN 6359
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	ADB

Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC

Accessories

Pull stud 45° sealed suitable for steep tapers 50	308760 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Pull stud 45° sealed suitable for steep tapers 50	308765 50
Pull-stud 60° sealed suitable for steep tapers 50	308780 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50