



Modular vice, Jaw width A: 150/3mm



Order data

Order number	362100 150/3
GTIN	2050001077493
Item class	35G

Description

Version:

- Simple mechanical actuation (up to 3.5 t).
- Easy adjustment of jaw opening.
- Machine vice with pull-down jaws.
- Case-hardened HRC 60.
- Parallelism 0.02 mm.

Supplied with:

Supplied with pull-down jaws, 1 workpiece backstop, 2 T-nuts No. 362160 size 16/16, 1 clamping wrench, 1 cross-bar wrench.

Note:

For other T-nuts see No. 362160.

Technical description

Colour code for suitable accessories	Gerardi 150
Transverse tenon slot n	16 mm
Base body height G	50 mm
Clamping range b	300 mm
Jaw height C	50 mm
Jaw width A	150 mm

Weight	40 kg
Overall length L	520 mm
Longitudinal tenon slot l	16 mm
maximum clamping force at 80 Nm	30 kN
Series	Gerardi 150
Type of product	Machine vice

Accessories

Pair of T-nuts T-slot dimension B / keyway 20/16 mm	362160 20/16
Square top jaw (piece) for jaw width 150 mm	362130 150
Prismatic jaw (piece) for jaw width 150 mm	362125 150
Longitudinally serrated front jaw (piece) for jaw width 150 mm	362146 150
Pair of T-nuts T-slot dimension B / keyway 12/16 mm	362160 12/16
Smooth front jaw, hard (piece) for jaw width 150 mm	362147 150
Centre jaw (piece) for jaw width 150 mm	362142 150
Complete clamping element (piece) for jaw width 150 mm	362144 150
Prismatic top jaw (piece) for jaw width 150 mm	362135 150
Pair of T-nuts T-slot dimension B / keyway 16/16 mm	362160 16/16
Modular element movable (piece) for jaw width 150 mm	362145 150
Modular element fixed (piece) for jaw width 150 mm	362150 150
Pair of clamps for jaw width 150 mm	362120 150
Smooth front jaw, soft (piece) for jaw width 150 mm	362148 150
Pair of T-nuts T-slot dimension B / keyway 14/16 mm	362160 14/16
Movable jaw (piece) for jaw width 150 mm	362143 150
Pair of T-nuts T-slot dimension B / keyway 18/16 mm	362160 18/16