



## Vernier caliper Vernier 1/50, Measuring range: 200mm



### Order data

Order number	410251 200
GTIN	4059192001599
Item class	43A

### Description

#### Version:

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Precision lapped measuring faces.

**Without** inch graduation.

#### Optional extras:

Thread table No. 412180 for caliper back.

### Technical description

Calibration	A1
Jaw length	50 mm
Packaging	Wallet
Scale divisions	0.02 mm
Measuring range	0 - 200 mm
Graduation	1/50 mm
Standard	ISO 13385
Depth gauge	flat
Depth gauge available	yes
Measurement deviation E MPE	$\pm 0.04$ mm

Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

## Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200