



Modular vice, Jaw width A: 200/3mm



Order data

Order number	362100 200/3
GTIN	2050001719522
Item class	35G

Description

Version:

- Simple mechanical actuation (up to 3.5 t).
- Easy adjustment of jaw opening.
- Machine vice with pull-down jaws.
- Case-hardened HRC 60.
- Parallelism 0.02 mm.

Supplied with:

Supplied with pull-down jaws, 1 workpiece backstop, 2 T-nuts No. 362160 size 16/16, 1 clamping wrench, 1 cross-bar wrench.

Note:

For other T-nuts see No. 362160.

Technical description

Longitudinal tenon slot l	16 mm
Base body height G	70 mm
Transverse tenon slot n	16 mm
Clamping range b	300 mm
Jaw height C	65 mm
Colour code for suitable accessories	Gerardi 200

Jaw width A	200 mm
Overall length L	595 mm
Weight	69 kg
maximum clamping force at 120 Nm	40 kN
Series	Gerardi 200
Type of product	Machine vice

Accessories

Pair of T-nuts T-slot dimension B / keyway 12/16 mm	362160 12/16
Pair of T-nuts T-slot dimension B / keyway 20/16 mm	362160 20/16
Pair of clamps for jaw width 200 mm	362120 200
Pair of T-nuts T-slot dimension B / keyway 18/16 mm	362160 18/16
Smooth front jaw, hard (piece) for jaw width 200 mm	362147 200
Smooth front jaw, soft (piece) for jaw width 200 mm	362148 200
Longitudinally serrated front jaw (piece) for jaw width 200 mm	362146 200
Pair of T-nuts T-slot dimension B / keyway 16/16 mm	362160 16/16
Pair of T-nuts T-slot dimension B / keyway 14/16 mm	362160 14/16