

**Vernier caliper with spring-loaded thumb-lock, Measuring range: 150mm****Order data**

Order number	410625 150
GTIN	4045197203021
Item class	41Z

Description**Version:**

Satin chromium plated anti-glare reading parts. Fine, high-contrast scale. Precision lapped measuring faces.

Thread table: Calipers table

Standard: ISO 13385

Reversible reading: mm / inch

Depth gauge: rectangular 3.7×1.3

Packaging: sturdy box

Calibration: A1

Scale divisions: 0.05 mm

Graduation: 1/20 mm

Graduation: 1/128 in

Measurement deviation E MPE: ± 0.03 mm

Jaw length: 40 mm

Technical description

Packaging	sturdy box
Jaw length	40 mm
Calibration	A1
Measuring range	0 - 150 mm
Scale divisions	0.05 mm
Graduation	1/20 mm

Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Measurement deviation E MPE	± 0.03 mm
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Plastic case Type MS150	412468 MS150
Synthetic leather case for vernier calipers	412500
Table for calipers	412180
Plastic case Type MS150	412470 MS150