



Vernier caliper Vernier 1/50, Measuring range: 300mm



Order data

Order number	410251 300
GTIN	4059192001605
Item class	43A

Description

Version:

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Precision lapped measuring faces.

Without inch graduation.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Packaging	Wallet
Jaw length	64 mm
Calibration	A1
Measuring range	0 - 300 mm
Scale divisions	0.02 mm
Graduation	1/50 mm
Standard	ISO 13385
Depth gauge	flat
Depth gauge available	yes
Measurement deviation E MPE	± 0.04 mm

Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Plastic case Type MS300	412470 MS300
-------------------------	--------------