



Vernier caliper parallax-free with rod type depth gauge, Measuring range: 150mm



Order data

Order number	410640 150
GTIN	4045197304001
Item class	41Z

Description

Version:

Satin chromium plated anti-glare reading parts. Fine, high-contrast scale, precision lapped measuring faces. Flat vernier scale for **parallax-free reading**.
With locking screw at top and rod type depth gauge.

Technical description

Measuring range	0 - 150 mm
Jaw length	40 mm
Packaging	sturdy box
Calibration	A1
Scale divisions	0.05 mm
Graduation	1/20 mm
Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	Ø 1.6
Depth gauge available	yes
Measurement deviation E MPE	± 0.05 mm

Scale chrome plated	yes
Depth gauge Ø	1.6 mm
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Table for calipers	412180
Synthetic leather case for vernier calipers	412500
Screw for depth gauge holder	412236