



Vernier caliper Vernier 1/20, Measuring range: 150 mm



Order data

| | |
|--------------|---------------|
| Order number | 410200 150 |
| GTIN | 4045197202932 |
| Item class | 41Z |

Description

Version:

Satin chromium plated anti-glare reading parts.

Locking screw at the top.

Thread table: Calipers table

Standard: DIN 862

Reversible reading: mm / inch

Packaging: Wallet

Calibration: A1

Scale divisions: 0.05 mm

Graduation: 1/20 mm

Graduation: 1/128 inch

Jaw length: 40 mm

Technical description

| | |
|-----------------|------------|
| Packaging | Wallet |
| Jaw length | 40 mm |
| Calibration | A1 |
| Scale divisions | 0.05 mm |
| Measuring range | 0 - 150 mm |
| Graduation | 1/20 mm |
| Graduation | 1/128 inch |

| | |
|------------------------|--------------------------|
| Reversible reading | mm / inch |
| Standard | DIN 862 |
| Depth gauge | flat |
| Locking | Locking screw at top |
| Measurement technology | analogue |
| Material | Stainless steel, INOX |
| all parts | hardened |
| Thread table | Calipers table |
| Type of product | Vernier caliper standard |

Services

| | |
|--|------------|
| Calibration Calipers / depth gauges maximum measuring range 200 mm | 011030 200 |
| Labelling laser-etched Type | 018940 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm | 011050 200 |
| Calibration Calipers / depth gauges maximum measuring range 200 mm | 021000 200 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm | 021010 200 |

Accessories

| | |
|---|--------------|
| Plastic case Type MS150 | 412468 MS150 |
| Synthetic leather case for vernier calipers | 412500 |
| Table for calipers | 412180 |
| Plastic case Type MS150 | 412470 MS150 |