



## Vernier caliper Vernier 1/20, Measuring range: 200mm



### Order data

Order number	410200 200
GTIN	4045197519269
Item class	41Z

### Description

#### Version:

Satin chromium plated anti-glare reading parts.

Locking screw at the top.

#### Supplied with:

Including thread table No. 412180 for caliper back.

### Technical description

Packaging	Wallet
Jaw length	50 mm
Measuring range	0 - 200 mm
Calibration	A1
Scale divisions	0.05 mm
Graduation	1/20 mm
Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Depth gauge available	yes
Measurement deviation E MPE	± 0.05 mm

Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

### Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200