

Mitutoyo
Vernier caliper, Measuring range: 150mm

Order data

Order number	410300 150
GTIN	4946368530000
Item class	44A

Description
Version:

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Without inch graduation.

Precision ground measuring faces.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Length of cross tips	21 mm
Scale divisions	0.05 mm
Jaw length	40 mm
Calibration	A1
Packaging	Wallet
Measuring range	0 - 150 mm
Graduation	1/20 mm
Standard	ISO 13385
Weight	143 g
Depth gauge	rectangular 3.7×1.4

Depth gauge available	yes
Measurement deviation E MPE	± 0.05 mm
Scale chrome plated	yes
Locking	Locking screw at top
Guidance	Raised slides
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Locking screw M2.6	410410
Synthetic leather case for vernier calipers	412500
Depth gauge holder, metal with 2 screws	412120