



## Vernier caliper Vernier 1/20, Measuring range: 300mm



### Order data

Order number	410200 300
GTIN	4045197519207
Item class	41Z

### Description

#### Version:

Satin chromium plated anti-glare reading parts.

Locking screw at the top.

Thread table: Calipers table

Standard: ISO 13385

Reversible reading: mm / inch

Depth gauge: rectangular 4.7×1.8

Packaging: Wallet

Calibration: A1

Scale divisions: 0.05 mm

Graduation: 1/20 mm

Graduation: 1/128 in

Measurement deviation E MPE: ± 0.08 mm

Jaw length: 64 mm

### Technical description

Scale divisions	0.05 mm
Calibration	A1
Packaging	Wallet
Measuring range	0 - 300 mm
Jaw length	64 mm
Graduation	1/20 mm

Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	rectangular 4.7×1.8
Depth gauge available	yes
Measurement deviation E MPE	± 0.08 mm
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

## Services

Calibration Calipers / depth gauges maximum measuring range 300 mm	011030 300
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	011050 300
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300

## Accessories

Plastic case Type MS300	412470 MS300
Plastic case Type MS300	412468 MS300