

Mitutoyo**Vernier caliper, Measuring range: 150Hm****Order data**

Order number	410300 150HM
GTIN	4946368110400
Item class	44A

Description**Version:**

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Without inch graduation.

Precision ground measuring faces. With **carbide** tipped jaws.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Jaw length	40 mm
Measuring range	0 - 150 mm
Calibration	A1
Length of cross tips	17 mm
Scale divisions	0.05 mm
Measurement face	Carbide-tipped anvils
Packaging	Wallet
Graduation	1/20 mm
Standard	ISO 13385
Weight	145 g

Depth gauge	rectangular 3.7×1.4
Depth gauge available	yes
Measurement deviation E MPE	± 0.05 mm
Scale chrome plated	yes
Locking	Locking screw at top
Guidance	Raised slides
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Depth gauge holder, metal with 2 screws	412120
Synthetic leather case for vernier calipers	412500
Locking screw M2.6	410410