

Mahr

Digital caliper starter pack with stick, Measuring range: 150STARTmm



Order data

Order number	402738 150START
GTIN	4059192064372
Item class	43A

Description

Version:

Functions: ON/OFF, AUTO-ON/OFF, HOLD (saving the measured value), RESET (zeroing the display), PRESET (unit of measure preset), mm/inch, reference system, LOCK function (keyboard lock), DATA (data transmission)

- **Integral radio transmitter**
- **Immediately ready for measurement due to the reference system**
- **Outstandingly resistant to dust, coolant fluids and lubricants: Protection class IP67**
- **Power supply: Battery, working life approx. 3 years (approx. 0.5 years if wireless transmission is used)**
- **Lapped slides**
- **Beam and slide of hardened stainless steel**

Version of the advertising text:

Very large LCD display with 11 mm character height. Integral i-wi wireless data interface. Resistant to dust and moisture. Service life approx. 3 years.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032. i-wi radio receiver no. 498912.

Note:

Download the MarCom Professional 5.2 software now free of charge at www.mahr.com/marcom

Technical description

Data sheet

Reversible reading	mm / inch
Calibration	A1
Depth gauge available	yes
Jaw length	40 mm
Auto switch-off	yes
Error limit	0.03 mm
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Working time	3 years
Depth gauge	flat
Standard	DIN 862
Measured value saving	MAHR Reference Lock system
Scale divisions	0.01 mm
#Article no of the battery / rechargeable battery fitted	1 pc. CR2032
#Number of batteries contained	1
Battery type	Button cell
IP Index of Protection	IP 67
Power supply	Battery-powered
International size	CR2032
Interface	MAHR i-wi radio system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/402738-150START>